

AQUARIUS HIGH NECK SV

Brushed with Copper Tails

AT03-032

Fixing Fixing length

The Aquarius range incorporate simple and modern design, with the latest electronic functionality.

Sensor-operated for maximum hygiene and efficiency. 5-litres per minute integrated flow-control. (Standard 5LPM, Other flow rates available)

 $\label{thm:condition} Automatic purge function, Sensor range adjustment, Wave on/wave off function, Anti Vandal and Lock Out functions, Chlorination function.$


Single mixed feed connection by Copper Tails (10mm Connection). External TMV required. Brushed finish.

Requires a Station kit to operate. Station kits available in Single Station Battery or Mains Single Station, 2 Station or 3 Station for multiple connections. Refer to Station kit Data sheets.

PRODUCT NUMBER	
AT03-032 Brushed	Aquarius High Neck SV no touch tap
TECHNICAL DATA	
Type of tap	Aquarius High Neck SV
Material	316 Stainless Steel
Surface finish	Brushed
Gross weight	1.25 kg
Type of operation	No Touch Sensor
Type of mounting	Deck mounted
Type of mixing	Additional TMV may be required
Automatic purge	Yes* - Default: OFF
	Options: 3, 6, 12, 24, 36 & 48 hours
Purge run time	Default 1 min*
	Options: OFF, 30 secs, 1, 2, 4 & 8 mins
Spout projection / Spout height	130mm / 101mm
Minimum flow pressure	1.00 bar (Lower pressure station kits available)
Volume flow rate at 3 bar	5LPM (Other flow rates available)
Adjustable run time	Yes* - Default: 2 secs
	Options: 2, 5, 10, 15, 20, 30 secs For Academic Use On
Water connection	10mm Copper Tails SolidWalfMcGlasdidatlEditionition.
Anti-Vandal function	Yes For Acadeside Mise Only Only.
Lock out function	Default OFF*
	Options: OFF, 4, 6, 8 & 10 operations
Chlorination function	Yes* - Default 2 mins
	Options: 1, 2, 3, 4, 5, 10, 20 & 30 mins
Battery or mains station kit	Single Battery: AT00-001
	Single Mains: AT00-002
	- Other options available. Contact DVS.
Working pressure	1-10 Bar (For Low / High pressure, Contact DVS.)
Max working temperature	60°C For Acade

Up to 50mm with flange nut





Last Updated: 2015-08-18, Dart Valley Systems





^{* (}Set By Handheld Programmer)